

Dry Gauges



ABS Case, Bottom Connection

Part No.	Type	Case Dia.	Case	Window	Movement	Bourdon Tube	Connection	Entry	Range	Operating Temp.	Accuracy
G50-01B	Dry	50MM	Plastic Abs	Acrylic	Brass	Phosphor Bronze	Brass	Bottom BSPT 1/8"	0-1 BAR / PSI	Ambient -20 + 60°C	2.50%
G50-02B	Dry	50MM	Plastic Abs	Acrylic	Brass	Phosphor Bronze	Brass	Bottom BSPT 1/8"	0-2 BAR / PSI	Ambient -20 + 60°C	2.50%
G50-04B	Dry	50MM	Plastic Abs	Acrylic	Brass	Phosphor Bronze	Brass	Bottom BSPT 1/8"	0-4 BAR / PSI	Ambient -20 + 60°C	2.50%
G50-06B	Dry	50MM	Plastic Abs	Acrylic	Brass	Phosphor Bronze	Brass	Bottom BSPT 1/8"	0-6 BAR / PSI	Ambient -20 + 60°C	2.50%
G50-10B	Dry	50MM	Plastic Abs	Acrylic	Brass	Phosphor Bronze	Brass	Bottom BSPT 1/8"	0-10 BAR / PSI	Ambient -20 + 60°C	2.50%
G50-12B	Dry	50MM	Plastic Abs	Acrylic	Brass	Phosphor Bronze	Brass	Bottom BSPT 1/8"	0-12 BAR / PSI	Ambient -20 + 60°C	2.50%
G50-02C	Dry	50MM	Plastic Abs	Acrylic	Brass	Phosphor Bronze	Brass	Bottom BSPT 1/4"	0-2 BAR / PSI	Ambient -20 + 60°C	2.50%
G50-04C	Dry	50MM	Plastic Abs	Acrylic	Brass	Phosphor Bronze	Brass	Bottom BSPT 1/4"	0-4 BAR / PSI	Ambient -20 + 60°C	2.50%
G50-06C	Dry	50MM	Plastic Abs	Acrylic	Brass	Phosphor Bronze	Brass	Bottom BSPT 1/4"	0-6 BAR / PSI	Ambient -20 + 60°C	2.50%
G50-10C	Dry	50MM	Plastic Abs	Acrylic	Brass	Phosphor Bronze	Brass	Bottom BSPT 1/4"	0-10 BAR / PSI	Ambient -20 + 60°C	2.50%
G50-12C	Dry	50MM	Plastic Abs	Acrylic	Brass	Phosphor Bronze	Brass	Bottom BSPT 1/4"	0-12 BAR / PSI	Ambient -20 + 60°C	2.50%
G100-04B	Dry	100MM	Plastic Abs	Acrylic	Brass	Phosphor Bronze	Brass	Bottom BSPT 3/8"	0-4 BAR / PSI	Ambient -20 + 60°C	2.50%
G100-06B	Dry	100MM	Plastic Abs	Acrylic	Brass	Phosphor Bronze	Brass	Bottom BSPT 3/8"	0-6 BAR / PSI	Ambient -20 + 60°C	2.50%
G100-10B	Dry	100MM	Plastic Abs	Acrylic	Brass	Phosphor Bronze	Brass	Bottom BSPT 3/8"	0-10 BAR / PSI	Ambient -20 + 60°C	2.50%
G100-14B	Dry	100MM	Plastic Abs	Acrylic	Brass	Phosphor Bronze	Brass	Bottom BSPT 3/8"	0-14 BAR / PSI	Ambient -20 + 60°C	2.50%

